# The New Standard In Healthcare Printing Solutions



A clinical-ready, compact, 2" printer designed for patient safety and compliance

**KEY FEATURES AND BENEFITS** 

# **Easy Operation Permits More Patient-Focused Time**

- Simple drop-in media loading
- Transparent media window allows users to easily monitor media reserves
- Tool-free maintenance
- Easy adjust sensor for compatibility with various media

# **Reduce Medical Missteps**

- Direct thermal for HIPAA compliance
- Clinical-ready anti-microbial plastic casing
- Conducive for the use of disinfectant cleansers


# **Accurate Patient Information**

- Cerner validated
- Easily integrates with existing HIS/EMR systems

# **Expediting Patient Workflows**

- Print on Demand:
  - SATO's SoftTouch wristbands
  - Laboratory specimen labels
  - In-patient chart labeling
- The ability to control and configure many printers within the user environment
- Standard on-board emulations for easier integration
- Up to forty-three percent faster print speeds than the market average





PRINTER MODEL	WS208	WS212
Print Resolution	203 dpi (8 dots/mm)	300 dpi (12 dots/mm)
Print Speed	2, 3, 4, 5, 6, 7 inches/sec (50, 76, 101, 127, 152, 177 mm/sec) 2 & 3ips for peel off mode	2, 3, 4, 5 inches/sec (50, 76, 101, 127 mm/sec) 2 & 3ips for peel off mode

# **PRINT SPECIFICATIONS**

#### Method

Direct Thermal

#### Mode

Standard: Continuous mode, Tear-off mode Optional: Cutter mode, Peel Present mode

#### **MEDIA SPECIFICATIONS**

# **Sensor Type**

Reflective Sensor (Movable), Transmissive sensor, Head Open Switch

# Media Type

Roll

# Print Area - Maximum Length

WS208 - 100" (2,540mm) WS212 - 50" (1,270 mm)

# **Print Area - Minimum Length**

0.39" (10mm);

Min. length:1.0" (25mm) for cutter/peeler options

# Print Area - Width

0.47" (12 mm) to 2.36" (60 mm)

#### **Alianment**

Centered

## **Roll Diameter**

5"(127mm) OD on a 1"/1.5" (25.4/38 mm) ID core 4.5"(115mm) OD on a 0.5" (12.7mm) ID core

CANADA

# Wind

Supports both wind in/wind out media

# **SATO Genuine Consumables**

For maximum print quality and optimum use, SATO recommends the use of SATO genuine consumables.

# **MEMORY & PROCESSING**

#### On-Board Memory

Standard Memory (Flash ROM): 16 MB User Memory: 8 MB Standard Memory (SDRAM): 32 MB USB storage up to 32 GB (FAT32 format only)

# **CPU Type**

32 bit RISC microprocessor

# **USER FRIENDLY SUPPORT TOOLS**

# **LED Indicator**

2 LEDs indicators Multicolor, Button x 1

# **Emulation**

SZPL®, SEPL®, SDPL®

\*Contact your SATO Sales Manager for more information/requirements

### **OPTIONS**

Peel Present, Full Cutter, WLAN

# FONT SPECIFICATIONS

# Internal Fonts

Bitmap support fonts of SZPL®, SEPL®, SDPL®

# **Label Editing**

Windows Driver (Windows Vista/ Win 7/ Win 8/ Win 10), BarTender® from Seagull Scientific, Nice Label

# Utility

Network Printer Management Tool

# **COMMUNICATION INTERFACES SPECIFICATIONS**

#### Standard

USB hosts (Type A) For Firmware Update, USB device (Type B), Fast Ethernet supporting: (IPv4/IPv6, WINS/Netbios)

# **Optional Wireless**

CARIBBEAN

Bluetooth 4.2, WLAN (IEEE802.11 b/g/n)

# **BARCODE SYMBOLOGIES**

#### **Barcodes**

#### Linear

Code 39, Code 93, Code 128 (ISBT128), CODABAR (NW-7), EAN8/13, GS1 DataBar™, GS1-128 (UCC/EAN128), Interleaved 2/5, Industrial 2/5, JAN8/13, Matrix 2/5, MSI, POSTNET™, UPC-A/E

#### 2D Symbologies

PDF417, Micro PDF, Maxi Code, GS1 Data Matrix, Data Matrix (ECC200), QR Code, Composite Symbologies, Aztec

# **OPERATING & ENVIRONMENT CHARACTERISTICS**

# Electrical Requirements

Voltage: AC 100 V ~ 240 V ± 10 % (full range) Frequency:  $50 \, \text{Hz} - 60 \, \text{Hz} \pm 5 \, \%$ 

# **Standards & Agency Approvals**

FCC, cTUVus, CB, CE Marking, Wireless IEEE

# **Environment**

# Operating

41°F to 104°F (5 °C to 40 °C)

25 %RH ~ 85 %RH (Without Condensation)

-4°F to 140°F (-20 °C to 60 °C)

10 %RH ~ 90 %RH (Without Condensation)

# PHYSICAL CHARACTERISTICS

# Weight

2.2 lbs. (1 kgs)

#### **Dimensions**

W 4.56" (116 mm) H 6.69" (170 mm) D 8.46" (215 mm)



SATO AMERICA CORPORATE

14125 South Bridge Circle Charlotte, NC 28273 Phone: (704) 644-1650 Fax: (704) 644-1662 sales-sal@sato-global.com **LABEL MANUFACTURING, SERVICE & SALES** UNITED STATES MEXICO CENTRAL AMERICA

Patientc2Safety

trademark of SATO Holdings Corporation and its subsidiaries in Japan, the U.S. and other countries. All other trademarks are the property of their respective owners.